

## DUPLI-COLOR NEON SPRAY

## Technical Information



Fast-drying acrylic laquer in fluorescent colours for professional decoration works on all kinds of materials.

**Ord.-no:** 194818, 194825, 194832, 194856, 556944, 626142, 626173, 626159, 626166, 880612, 194818-AT, 194818-DG, 194825-AT, 194825-DG, 194825-DW, 194832-AT, 194832-DG, 194832-DW, 556944-DW, 626142-DF, 626142-DW, 626142-ER, 626159-DF, 626166-DF, 626166-DW, 626173-DF

### Quality & properties

- High-grade acrylic quality
- Very good coverage
- Excellent adhesion on many surface
- Also suitable for polystyrene
- Good flow, smooth surface
- Suitable for indoors and outdoors applications
- Resistant to wipint
- Weather-resistant
- Limited light-proof and UV-resistant. The intensity of luminosity decreases by-and-by. With a clear varnish coating you can delay this effect a bit.
- Scratch-, shock- and impact-resistant

### Physical & chemical data

- Base: Acrylic resin
- Colourname:
  - yellow
  - green
  - signal red
  - blue
  - pink
- Degree of gloss: mat GU
- Efficiency:
  - 400 ML – 0.8 - 1.0 m<sup>2</sup>
  - 150 ML – 0.3 - 0.4 m<sup>2</sup>
- Dry to touch: 30 min
- Dust dry: 15 min
- Completely dry:
  - 24 min
  - 2 min
- Overcoatable: 1-2 h
- Surfaces: Metal, wood, glass, ceramic, polystyrene, eternite, concrete, stone, paper, cardboard, coatable hard plastics, flowers etc.
- Minimum Working Temperature: 10 °C
- Maximum Working Temperature: 25 °C
- Flash point: n.a.
- Storage stability: 10 y
- Content:
  - 400 ML
  - 150 ML

---

### How to use

Remove rust and dirt.  
The ground has to be clean, dry and free from fat.  
Cover areas not to be painted.  
Apply a white primer, e.g. DUPLI-COLOR Primer white. (Not if used on polystyrene!)  
Before use, shake can for 3 minutes.  
Test spray at an invisible spot.  
Spray from a distance of 12-15 cm several thin coats.  
Do not spray over surfaces which are painted with synthetic resin lacquer!

### Environmentally sound

European Aerosols is committed to apply formulations without restricted or critical ingredients and to achieve best possible performance. The caps and packagings are made of recyclable material.

### Disposal

Only the completely emptied cans should be put into the recycling skip or appropriate container for reclaimable refuse. Cans which are not empty should be disposed off as "special refuse".

### Marking/Labelling

All products made by European Aerosols comply with the actual labelling regulations according to Preparation Guideline 1999/45/EG. All aerosols correspond to TRGS 200 and TRG 300 as well as to aerosol guideline 75/324/EWG in the actually valid version.

**As of May 21, 2025** – This release replaces all eventually earlier issued versions.